

TECHNICAL DATA SHEET

Part No. 151-01404
Article No. 151-01404
Type BCBRT55M



HellermannTyton connector clips, for oval holes, are mounted simply by pushing them onto the corresponding clip. The clips provide a wide range of mounting options with anti-rattle and anti-rotation features. The fir tree locks into place when inserted into the hole palpably and ensures a secure fixing at all times.

Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature, 500h	+329°F (+165°C)
Operating Temperature, 1000h	+320°F (+160°C)
Operating Temperature, 5000h	+257°F (+125°C)
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Natural (NA)
Pkg. Qty.	1000
Carton Qty.	1000
Customs Number	3926909988

Height (imperial)	0.62 "
Height (metric)	15.8 mm
Length (imperial)	2.79 "
Length (metric)	70.9 mm
Offset Length (imperial)	2.17 "
Offset Length (metric)	55.15 mm
Width (imperial)	1.97 "
Width (metric)	50.0 mm

RoHS ✓