

TECHNICAL DATA SHEET

Part No. 151-01531
Article No. 151-01531
Type RCINSERTB



Soft Inserts snap into the body of HellermannTyton's Ratchet Clamps. They provide an added level of protection for sensitive bundles, especially in high-vibration applications.

Material	Thermoplastic Elastomer (TPE)
Operating Temperature	-40°F to +194°F (-40°C to +90°C)
Flammability	UL 94 HB
Plenum Rating	AH-2
UV Resistant	Yes
Use Conditions	For Indoor Use Only
Color	Black (BK)
Pkg. Qty.	100
Carton Qty.	400
Customs Number	3926909988

Max. Bundle Diameter (imperial)	0.61 "
Max. Bundle Diameter (metric)	15.5 mm
Min. Bundle Diameter (imperial)	0.34 "
Min. Bundle Diameter (metric)	8.7 mm
Width (imperial)	0.79 "
Width (metric)	20.0 mm

RoHS ✓

