

# TECHNICAL DATA SHEET

**Part No.** 151-01565  
**Article No.** 151-01565  
**Type** BCAA



<b>Material</b>	Polyamide 6.6, glass fiber reinforced (PA66GF30), Polyamide 6.6, glass-fibre reinforced (PA66GF35)
<b>Adhesive</b>	Acrylic foam
<b>Operating Temperature</b>	-40°F to +284°F (-40°C to +140°C)
<b>Flammability</b>	UL 94 HB
<b>UV Resistant</b>	Yes
<b>Use Conditions</b>	For Indoor and Outdoor Use
<b>Color</b>	Black (BK), Green (GN)
<b>Pkg. Qty.</b>	200
<b>Carton Qty.</b>	600
<b>Customs Number</b>	3926909988

<b>Fixation Method</b>	Edge Clip
<b>Height (imperial)</b>	1.68 "
<b>Height (metric)</b>	42.7 mm
<b>Length (imperial)</b>	1.21 "
<b>Length (metric)</b>	30.8 mm
<b>Max. Cable Tie Width (imperial)</b>	0.59 "
<b>Max. Cable Tie Width (metric)</b>	15.0 mm
<b>Panel Thickness (imperial)</b>	0 - 0.20 "
<b>Panel Thickness (metric)</b>	0 - 5.0 mm
<b>Width (imperial)</b>	1.13 "
<b>Width (metric)</b>	28.6 mm

