

# TECHNICAL DATA SHEET

**Part No.** 151-01566  
**Article No.** 151-01566  
**Type** BCBLGA



The Wedge Clip, paired with any HellermannTyton heavy duty Cable Tie, routes cables along a frame or rail in vertical or horizontal applications. A robust design and durable materials make it ideal for extreme-duty applications. The integrated wedge mechanism slides along a stepped grade until snug against the mounting surface. Inside the clip is a 3M™ VHB™ (Very High Bond) adhesive pad, which actually builds strength over time. This holds the clip to the work surface instantly, enabling installers to place it into position without worrying about it falling off prior to fastening. The combination of adhesive and the clip's vice-like compression result in incredible extraction force without the need to drill holes. The Wedge Clip is offered in three sizes.

|  |               |
|--|---------------|
| <b>Fixation Method</b>                 | Edge Clip     |
| <b>Height (imperial)</b>               | 1.68 "        |
| <b>Height (metric)</b>                 | 42.7 mm       |
| <b>Length (imperial)</b>               | 1.21 "        |
| <b>Length (metric)</b>                 | 30.8 mm       |
| <b>Max. Cable Tie Width (imperial)</b> | 0.59 "        |
| <b>Max. Cable Tie Width (metric)</b>   | 15.0 mm       |
| <b>Panel Thickness (imperial)</b>      | 0.16 - 0.35 " |
| <b>Panel Thickness (metric)</b>        | 4.0 - 9.0 mm  |
| <b>Width (imperial)</b>                | 1.13 "        |
| <b>Width (metric)</b>                  | 28.6 mm       |

|                              |  |
|------------------------------|--|
| <b>Material</b>              | Polyamide 6.6, glass fiber reinforced (PA66GF30) |
| <b>Adhesive</b>              | Acrylic foam                                     |
| <b>Operating Temperature</b> | -40°F to +284°F (-40°C to +140°C)                |
| <b>Flammability</b>          | UL 94 HB   |
| <b>UV Resistant</b>          | Yes  |
| <b>Use Conditions</b>        | For Indoor and Outdoor Use                       |
| <b>Color</b>                 | Black (BK)                                       |

|                       |            |
|-----------------------|------------|
| <b>Pkg. Qty.</b>      | 200        |
| <b>Carton Qty.</b>    | 600        |
| <b>Customs Number</b> | 3926909988 |

RoHS 