

TECHNICAL DATA SHEET

Part No. 151-01634
Article No. 151-01634
Type MB5A4



MB5A4 adhesive mounts are for use with HellermannTyton T18 - T150 Series cable ties to provide stability when securing bundles. The high-heat, high-bond acrylic adhesive-backed mounts can be used to secure a bundle and have two predrilled holes to extend mounting options.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Adhesive	Acrylic foam
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature, 500h	+329°F (+165°C)
Operating Temperature, 1000h	+320°F (+160°C)
Operating Temperature, 5000h	+257°F (+125°C)
Flammability	UL 94 HB
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	250
Carton Qty.	2000
Customs Number	3926909988

Fixation Method	Adhesive
For Cable Tie Series	T18 - T150
Height (imperial)	.28 "
Height (metric)	7.1 mm
Length (imperial)	1.49 "
Length (metric)	37.7 mm
Max. Static Load (imperial)	2.1 lbf-ft
Maximum Static Load (N)	9.341 N
Width (imperial)	1.49 "
Width (metric)	37.7 mm

