

# TECHNICAL DATA SHEET

**Part No.** 151-01749  
**Article No.** 151-01749  
**Type** MOC10FT6.5



The MOC with Round Fir Tree features HellermannTyton's unique retention clip with an integrated fir tree to fit securely in a 6.5 (+/-0.4) mm hole. The mount delivers a low insertion force while exhibiting high extraction resistance for a secure mounting point against a panel.

<b>Material</b>	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
<b>Operating Temperature</b>	-40°F to +221°F (-40°C to +105°C)
<b>Flammability</b>	UL 94 HB
<b>Halogen Free</b>	Yes
<b>UV Resistant</b>	Yes
<b>Use Conditions</b>	For Indoor and Outdoor Use
<b>Color</b>	Black (BK)
<b>Pkg. Qty.</b>	7500
<b>Carton Qty.</b>	7500
<b>Customs Number</b>	3926909988

<b>Depth (imperial)</b>	0.39 "
<b>Depth (metric)</b>	10.0 mm
<b>Height (imperial)</b>	1.39 "
<b>Height (metric)</b>	35.4 mm
<b>Max. Bundle Diameter (imperial)</b>	0.45 "
<b>Max. Bundle Diameter (metric)</b>	11.5 mm
<b>Min. Bundle Diameter (imperial)</b>	0.37 "
<b>Min. Bundle Diameter (metric)</b>	9.5 mm
<b>Mounting Hole Diameter (imperial)</b>	0.24 - 0.27 ", 0.25 " (HEXAGONAL)
<b>Mounting Hole Diameter (metric)</b>	6.1 - 6.9 mm, 6.35 mm (hexagonal)
<b>Panel Thickness (imperial)</b>	0.02 - 0.22 "
<b>Panel Thickness (metric)</b>	0.6 - 5.5 mm

