

TECHNICAL DATA SHEET

Part No. 151-01884
Article No. 151-01884
Type BCSFTOVAL2



Half-length tape clip with oval fir tree mount accommodates tape or cable ties to fasten bundles or cables to a surface. The oval fir tree supports a variety of hole sizes and panel thicknesses. Materials perform optimally in a wide range of environmental and temperature conditions.

Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature, 500h	+329°F (+165°C)
Operating Temperature, 1000h	+320°F (+160°C)
Operating Temperature, 5000h	+257°F (+125°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Natural (NA)
Pkg. Qty.	8000
Carton Qty.	8000
Customs Number	3926909988

Fixation Method	Fir Tree for oval holes
Height (imperial)	0.46 "
Height (metric)	11.6 mm
Length (imperial)	1.52 "
Length (metric)	38.7 mm
Mounting Hole Diameter (imperial)	0.24 x 0.48 ", 0.25 x 0.50 ", 0.27 x 0.47 "
Mounting Hole Diameter (metric)	6.2 x 12.2 mm, 6.5 x 12.5 mm, 6.5 x 13.0 mm, 7.0 x 12.0 mm
Panel Thickness (imperial)	0.02 - 0.10 "
Panel Thickness (metric)	0.6 - 2.5 mm
Tape Bar Length (imperial)	1.52 "
Tape Bar Length (metric)	38.7 mm
Width (imperial)	0.29 "
Width (metric)	7.37 mm

HF ✓

RoHS ✓