

TECHNICAL DATA SHEET

Part No. 151-01888
Article No. 151-01888
Type BCFTOVALXL



HellermannTyton's bundling clips allow a harness to be routed around a corner and attached to the panel at this location.

Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature, 500h	+329°F (+165°C)
Operating Temperature, 1000h	+320°F (+160°C)
Operating Temperature, 5000h	+257°F (+125°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Natural (NA)
Pkg. Qty.	3000
Carton Qty.	3000
Customs Number	3926909988

Fixation Method	Fir Tree for oval holes
Height (imperial)	0.97 "
Height (metric)	24.58 mm
Length (imperial)	0.53 "
Length (metric)	13.4 mm
Mounting Hole Diameter (imperial)	0.24 x 0.48 ", 0.25 x 0.50 ", 0.27 x 0.47 "
Mounting Hole Diameter (metric)	6.2 x 12.2 mm, 6.5 x 12.5 mm, 6.5 x 13.0 mm, 7.0 x 12.0 mm
Panel Thickness (imperial)	0.02 - 0.43 "
Panel Thickness (metric)	0.6 - 11.0 mm
Tape Bar Length (imperial)	2.28 "
Tape Bar Length (metric)	58.0 mm
Width (imperial)	0.38 "
Width (metric)	9.6 mm

HF ✓

RoHS ✓