

TECHNICAL DATA SHEET

Part No. 151-02013
Article No. 151-02013
Type RCD180MM8SS



The Ratchet P-Clamp family offers versatility when managing wires, cables and hoses. The robust design and durable materials make it ideal for heavy duty applications, both indoors and out. The one-piece adjustable clamp can be closed by hand to the desired diameter. The release feature provides easy and nondestructive removal of cables simply by using a flat-head screwdriver. This nondestructive release allows the clamp to be reused without removing or replacing any bolts or screws.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV), Stainless Steel (SS304)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature, 500h	+329°F (+165°C)
Operating Temperature, 1000h	+320°F (+160°C)
Operating Temperature, 5000h	+257°F (+125°C)
Flammability	UL 94 HB
Halogen Free	Yes
Plenum Rating	AH-2
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	140
Carton Qty.	140
Customs Number	3926909988

Angle	180 °
Length (imperial)	8.01 "
Length (metric)	203.45 mm
Length 2 (imperial)	5.41 "
Length 2 (metric)	137.5 mm
Max. Bundle Diameter (imperial)	2.01 "
Max. Bundle Diameter (metric)	51.0 mm
Min. Bundle Diameter (imperial)	1.42 "
Min. Bundle Diameter (metric)	36.0 mm
Min. Tensile Strength (imperial)	100 lbs
Min. Tensile Strength (metric)	445 N
Mounting Hole Centers (imperial)	3.62 "
Mounting Hole Centers (metric)	92.0 mm
Mounting Hole Diameter (imperial)	0.327 "
Mounting Hole Diameter (metric)	8.31 mm
Width (imperial)	1.37 "
Width (metric)	34.9 mm

