

TECHNICAL DATA SHEET

Part No. 151-02083
Article No. 151-02083
Type MOC5FT6.5



The MOC with Round Fir Tree features HellermannTyton's unique retention clip with an integrated fir tree to fit securely in a 6.5 (+/-0.4) mm hole. The mount delivers a low insertion force while exhibiting high extraction resistance for a secure mounting point against a panel.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	5000
Carton Qty.	5000
Customs Number	3926909988

Depth (imperial)	0.39 "
Depth (metric)	10.0 mm
Height (imperial)	1.04 "
Height (metric)	26.3 mm
Max. Bundle Diameter (imperial)	0.22 "
Max. Bundle Diameter (metric)	5.5 mm
Min. Bundle Diameter (imperial)	0.16 "
Min. Bundle Diameter (metric)	4.0 mm
Mounting Hole Diameter (imperial)	0.24 - 0.27 ", 0.25 " (HEXAGONAL)
Mounting Hole Diameter (metric)	6.1 - 6.9 mm, 6.35 mm (hexagonal)
Panel Thickness (imperial)	0.02 - 0.22 "
Panel Thickness (metric)	0.6 - 5.5 mm

