

TECHNICAL DATA SHEET

Part No. 151-02097
Article No. 151-02097
Type HDM500



The high-torque mount is designed for use with power-assisted impact wrenches and is molded with a heavy bushing to withstand the forces required to tighten grade 8 bolts. The arched H-profile of the saddle surface allows for a broad surface contact with the bundle, minimizing pinching and crushing of the bundles, and adjusts to a wide variety of bundle diameters when used with HellermannTyton heavy duty T120, T250, T255 and Wide Strap Cable Ties.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature, 500h	+329°F (+165°C)
Operating Temperature, 1000h	+320°F (+160°C)
Operating Temperature, 5000h	+257°F (+125°C)
Flammability	UL 94 HB
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	100
Carton Qty.	500
Customs Number	3926909988

Fixation Method	Screw Mounting and Rivet
Height (imperial)	0.81 "
Height (metric)	20.7 mm
Length (imperial)	1.85 "
Length (metric)	47.0 mm
Max. Cable Tie Width (imperial)	0.5 "
Max. Cable Tie Width (metric)	12.7 mm
Mounting Screw Type	1/2" (M12) Screw
Width (imperial)	1.0 "
Width (metric)	25.0 mm

