

TECHNICAL DATA SHEET

Part No. 151-02102
Article No. 151-02102
Type SAM400B-R



HellermannTyton's axial oval mount stands off bundles from frame rails and cross members to prevent them from rubbing and chafing. The axial oval mount accommodates cable ties up to 0.5" wide. The hole on the mount was designed to fit a 5/16" bolt.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature, 500h	+329°F (+165°C)
Operating Temperature, 1000h	+320°F (+160°C)
Operating Temperature, 5000h	+257°F (+125°C)
Flammability	UL 94 HB
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	500
Carton Qty.	500
Customs Number	3926909988

Fixation Method	Screw Mounting and Rivet
Height (imperial)	1.77 "
Height (metric)	44.9 mm
Length (imperial)	1.18 "
Length (metric)	29.9 mm
Max. Cable Tie Width (imperial)	0.5
Max. Cable Tie Width (metric)	12.7 mm
Mounting Screw Type	3/8" (M10) Screw
Width (imperial)	0.98 "
Width (metric)	25.0 mm

RoHS

