

TECHNICAL DATA SHEET

Part No. 151-02177
Article No. 151-02177
Type BCATC4



HellermannTyton's bundling clips allow a harness to be routed around a corner and attached to the panel at this location.

Material	Polyphenylene Sulfide (PPS)
Operating Temperature	-40°F to +302°F (-40°C to +150°C)
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Silver (SR)
Pkg. Qty.	2000
Carton Qty.	2000
Customs Number	3926909988

Fixation Method	Arrowhead
Height (imperial)	1.22 "
Height (metric)	30.94 mm
Length (imperial)	2.95 "
Length (metric)	75.0 mm
Mounting Hole Diameter (imperial)	0.46 - 0.51 "
Mounting Hole Diameter (metric)	11.7 - 13.0 mm
Panel Thickness (imperial)	0.53 - 0.59 "
Panel Thickness (metric)	13.5 - 15.0 mm
Tape Bar Length (imperial)	2.95 "
Tape Bar Length (metric)	75.0 mm
Width (imperial)	0.45 "
Width (metric)	11.43 mm

RoHS 