

TECHNICAL DATA SHEET

Part No. 151-02189
Article No. 151-02189
Type MSC90



HellermannTyton's 90-Degree Metal Edge Clip provides an excellent alternative to managing wire and PV cables where plastic fasteners are not the preferred method. Designed for effortless insertion, this edge clip also has a high extraction force. The 90-degree configuration secures cables to a panel in a perpendicular orientation. Metal construction tolerates extreme environments, and a low-profile design allows the clip to be installed on a wide variety of module edges.

Material	Stainless Steel (SS304)
Operating Temperature	-112°F to +1000°F (-80°C to +538°C)
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Metal (ML)
Pkg. Qty.	100
Carton Qty.	5000
Customs Number	7326908695

Fixation Method	Edge Clip
Length (imperial)	0.73 "
Length (metric)	18.44 mm
Max. Cable Diameter (imperial)	0.276 "
Max. Cable Diameter (metric)	7.0 mm
Min. Cable Diameter (imperial)	0.161 "
Min. Cable Diameter (metric)	4.1 mm
Panel Thickness (imperial)	0.06 - 0.08 "
Panel Thickness (metric)	1.5 - 2.0 mm
Width (imperial)	0.460 "
Width (metric)	11.57 mm

