

TECHNICAL DATA SHEET

Part No. 151-02206
Article No. 151-02206
Type CC16R



Connector Clips feature various attachment point configurations to accommodate the many connectors on the market. They are first mated with a connector on a wire harness or cable assembly, then secured to a surface using the integrated mount. With so many configurations available, attachment surfaces can be a hole, edge, stud or even another harness assembly.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature, 500h	+329°F (+165°C)
Operating Temperature, 1000h	+320°F (+160°C)
Operating Temperature, 5000h	+257°F (+125°C)
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	5000
Carton Qty.	5000
Customs Number	3926909988

Fixation Method	Fir Tree for oval holes
Length (imperial)	1.18 "
Length (metric)	30.0 mm
Mounting Hole Diameter (imperial)	0.31 x 0.59 ", 0.31 x 0.55 "
Mounting Hole Diameter (metric)	8.0 x 14.0 mm, 8.0 x 15.0 mm
Panel Thickness (imperial)	0.02 - 0.12 "
Panel Thickness (metric)	0.6 - 3.0 mm
Width (imperial)	0.72 "
Width (metric)	18.2 mm

