

TECHNICAL DATA SHEET

Part No. 151-02255
Article No. 151-02255
Type PMB5



The PMB5 epoxy mount provides a reliable fastening solution in environments where screw installations are not permitted. Commonly used in the aerospace, railway, and renewable energy sectors, the PMB5's design enables secure mounting, even on uneven surfaces. This adhesive mount is specifically designed for use with paste or liquid adhesives, allowing for versatile and durable installation options.

Material	Polyamide 6.6 heat stabilized (PA66HS)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 V-2
Halogen Free	No
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	100
Carton Qty.	2000
Customs Number	3926909988

Fixation Method	Pasting / Stick
Height (imperial)	0.42 "
Height (metric)	10.7 mm
Length (imperial)	1.42 "
Length (metric)	36.0 mm
Width (imperial)	1.42 "
Width (metric)	36.0 mm

RoHS