

# TECHNICAL DATA SHEET

**Part No.** 151-02284  
**Article No.** 151-02284  
**Type** TCOP70x120



HellermannTyton pipe and hose clips offer simple and secure installation of pipes or hoses to panels. Simply push the pipe into the clip for a firm and secure fixing. These parts can also be connected together offering a greater choice of installation options.

|                              |                                                                  |
|------------------------------|------------------------------------------------------------------|
| <b>Material</b>              | Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS) |
| <b>Operating Temperature</b> | -40°F to +221°F (-40°C to +105°C)                                |
| <b>Flammability</b>          | UL 94 HB                                                         |
| <b>Halogen Free</b>          | Yes                                                              |
| <b>UV Resistant</b>          | No                                                               |
| <b>Use Conditions</b>        | For Indoor and Outdoor Use                                       |
| <b>Color</b>                 | Black (BK)                                                       |
| <b>Pkg. Qty.</b>             | 5000                                                             |
| <b>Carton Qty.</b>           | 5000                                                             |
| <b>Customs Number</b>        | 3926909988                                                       |

|                                          |                         |
|------------------------------------------|-------------------------|
| <b>Fixation Method</b>                   | Fir Tree for oval holes |
| <b>Length (imperial)</b>                 | 2.2 "                   |
| <b>Length (metric)</b>                   | 55.0 mm                 |
| <b>Mounting Hole Diameter (imperial)</b> | 0.28 - 0.47 "           |
| <b>Mounting Hole Diameter (metric)</b>   | 7.0 x 12.0 mm           |
| <b>Panel Thickness (imperial)</b>        | 0.02 - 0.24 "           |
| <b>Panel Thickness (metric)</b>          | 0.6 - 6.0 mm            |
| <b>Tape Bar Length (imperial)</b>        | 2.17 "                  |
| <b>Tape Bar Length (metric)</b>          | 55.0 mm                 |
| <b>Width (imperial)</b>                  | 0.35 "                  |
| <b>Width (metric)</b>                    | 9.0 mm                  |

