

TECHNICAL DATA SHEET

Part No. 151-02432
Article No. 151-02432
Type SOC8FT8



Tape clips are designed to provide simple and easy methods of securing cable bundles, hoses, or pipes.

Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature, 500h	+329°F (+165°C)
Operating Temperature, 1000h	+320°F (+160°C)
Operating Temperature, 5000h	+257°F (+125°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Natural (NA)
Pkg. Qty.	2500
Carton Qty.	2500
Customs Number	3926909988

Fixation Method	Fir Tree
Height (imperial)	0.88 "
Height (metric)	22.4 mm
Length (imperial)	2.4 "
Length (metric)	61 mm
Mounting Hole Diameter (imperial)	0.30 - 0.39 "
Mounting Hole Diameter (metric)	7.6 - 10.0 mm, M10 x 1.5
Offset Length (imperial)	0.625 "
Offset Length (metric)	15.9 mm
Panel Thickness (imperial)	0.02 - 0.22 "
Panel Thickness (metric)	0.6 - 5.5 mm
Tape Bar Length (imperial)	2.40 "
Tape Bar Length (metric)	61.0 mm
Width (imperial)	0.47 "
Width (metric)	12.0 mm

