

# TECHNICAL DATA SHEET

**Part No.** 151-02436  
**Article No.** 151-02436  
**Type** MSC2LP



Designed for more confined areas, HellermannTyton's Low Profile Metal Edge Clip provides an excellent alternative to managing wire and PV cables where plastic fasteners are not the preferred method. Designed for effortless insertion, the Metal Edge Clip has a high extraction force that tolerates extreme environments and provides assurance that the cables are secure on a panel. The Metal Edge Clip is simple to install and can easily be removed with a flathead screwdriver.

<b>Material</b>	Stainless Steel (SS304)
<b>Operating Temperature</b>	-112°F to +1000°F (-80°C to +538°C)
<b>Halogen Free</b>	Yes
<b>UV Resistant</b>	Yes
<b>Use Conditions</b>	For Indoor and Outdoor Use
<b>Color</b>	Metal (ML)
<b>Pkg. Qty.</b>	5000
<b>Carton Qty.</b>	5000
<b>Customs Number</b>	7326908695

<b>Fixation Method</b>	Edge Clip
<b>Length (imperial)</b>	0.67 "
<b>Length (metric)</b>	17.0 mm
<b>Max. Cable Diameter (imperial)</b>	0.276 "
<b>Max. Cable Diameter (metric)</b>	7.0 mm
<b>Min. Cable Diameter (imperial)</b>	0.161 "
<b>Min. Cable Diameter (metric)</b>	4.1 mm
<b>Panel Thickness (imperial)</b>	0.06 - 0.08 "
<b>Panel Thickness (metric)</b>	1.5 - 2.0 mm
<b>Width (imperial)</b>	0.375 "
<b>Width (metric)</b>	9.50 mm

