

TECHNICAL DATA SHEET

Part No. 151-02451
Article No. 151-02451
Type PC4X1-5X1



An ultra-secure routing clip connected to a round or oval fixing for easy insertion into an existing panel hole.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	10000
Carton Qty.	10000
Customs Number	3926909988

Height (imperial)	0.72 "
Height (metric)	18.2 mm
Length (imperial)	0.32 "
Length (metric)	8.2 mm
Max. Bundle Diameter (imperial)	0.2 "
Max. Bundle Diameter (metric)	5.0 mm
Min. Bundle Diameter (imperial)	0.16 "
Min. Bundle Diameter (metric)	4.0 mm

HF✓

RoHS✓