

# TECHNICAL DATA SHEET

**Part No.** 151-02457  
**Article No.** 151-02457  
**Type** SOBC25FT8



Tape clips are designed to provide simple and easy methods of securing cable bundles, hoses, or pipes.

<b>Material</b>	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
<b>Operating Temperature</b>	-40°F to +221°F (-40°C to +105°C)
<b>Flammability</b>	UL 94 HB
<b>UV Resistant</b>	Yes
<b>Use Conditions</b>	For Indoor and Outdoor Use
<b>Color</b>	Black (BK)
<b>Pkg. Qty.</b>	5000
<b>Carton Qty.</b>	5000
<b>Customs Number</b>	3926909988

<b>Fixation Method</b>	Fir Tree
<b>Height (imperial)</b>	0.7 "
<b>Height (metric)</b>	17.9 mm
<b>Length (imperial)</b>	2.36 "
<b>Length (metric)</b>	60.0 mm
<b>Mounting Hole Diameter (imperial)</b>	0.30 - 0.33 "
<b>Mounting Hole Diameter (metric)</b>	7.6 - 8.4 mm, M10 x 1.5
<b>Offset Length (metric)</b>	25.3 mm
<b>Panel Thickness (imperial)</b>	0.02 - 0.23 "
<b>Panel Thickness (metric)</b>	0.6 - 5.75 mm
<b>Tape Bar Length (imperial)</b>	2.36 "
<b>Tape Bar Length (metric)</b>	60.0 mm
<b>Width (imperial)</b>	1.377 "
<b>Width (metric)</b>	35.0 mm

