

# TECHNICAL DATA SHEET

**Part No.** 151-02458  
**Article No.** 151-02458  
**Type** CC11FTM6



Connector Clips feature various attachment point configurations to accommodate the many connectors on the market. They are first mated with a connector on a wire harness or cable assembly, then secured to a surface using the integrated mount. With so many configurations available, attachment surfaces can be a hole, edge, stud or even another harness assembly.

<b>Material</b>	Polyamide 4.6 (PA46)
<b>Operating Temperature</b>	-40°F to +266°F (-40°C to +130°C)
<b>UV Resistant</b>	No
<b>Use Conditions</b>	For Indoor Use Only
<b>Color</b>	Brown (BN)
<b>Pkg. Qty.</b>	5000
<b>Carton Qty.</b>	500 Bag
<b>Customs Number</b>	3926909988

<b>Fixation Method</b>	Fir tree for round holes
<b>Length (imperial)</b>	0.98 "
<b>Length (metric)</b>	24.9 mm
<b>Mounting Hole Diameter (imperial)</b>	0.24 "
<b>Mounting Hole Diameter (metric)</b>	M6
<b>Panel Thickness (imperial)</b>	0.05 - 0.18 "
<b>Panel Thickness (metric)</b>	1.3 - 4.5 mm
<b>Width (imperial)</b>	0.622 "
<b>Width (metric)</b>	15.8 mm