

TECHNICAL DATA SHEET

Part No. 151-02459
Article No. 151-02459
Type CC11FTM6



Connector Clips feature various attachment point configurations to accommodate the many connectors on the market. They are first mated with a connector on a wire harness or cable assembly, then secured to a surface using the integrated mount. With so many configurations available, attachment surfaces can be a hole, edge, stud or even another harness assembly.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature, 500h	+329°F (+165°C)
Operating Temperature, 1000h	+320°F (+160°C)
Operating Temperature, 5000h	+257°F (+125°C)
Flammability	UL 94 HB
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	5008
Carton Qty.	5000
Customs Number	3926909988

Fixation Method	Fir tree for round holes
Length (imperial)	0.98 "
Length (metric)	24.9 mm
Mounting Hole Diameter (imperial)	0.24 "
Mounting Hole Diameter (metric)	M6
Panel Thickness (imperial)	0.05 - 0.18 "
Panel Thickness (metric)	1.3 - 4.5 mm
Width (imperial)	0.622 "
Width (metric)	15.8 mm

RoHS 