

TECHNICAL DATA SHEET

Part No. 151-02501
Article No. 151-02501
Type LOC1014FT9x12



The Locking Omega Clip creates a full and secure lock completely around a wire bundle ranging from 5-25 mm. The fixating fir tree on this clip allows for the clip to be secured into a panel by utilizing a round or oval hole.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature, 500h	+329°F (+165°C)
Operating Temperature, 1000h	+320°F (+160°C)
Operating Temperature, 5000h	+257°F (+125°C)
Flammability	UL 94 HB
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)

Pkg. Qty.	500
Carton Qty.	500
Customs Number	3926909988

Height (imperial)	2.31 "
Height (metric)	58.57 mm
Max. Bundle Diameter (imperial)	0.55 "
Max. Bundle Diameter (metric)	14.0 mm
Min. Bundle Diameter (imperial)	0.39 "
Min. Bundle Diameter (metric)	10.0 mm
Mounting Hole Diameter (imperial)	0.35 x 0.55 ", 0.35 x 0.47 "
Mounting Hole Diameter (metric)	9.0 x 12.0 mm, 9.0 x 14.0 mm
Panel Thickness (imperial)	0.02 - 0.27 "
Panel Thickness (metric)	0.6 - 6.75 mm
Width (imperial)	0.47 "
Width (metric)	12.0 mm

RoHS 

