

TECHNICAL DATA SHEET

Part No. 151-02551
Article No. 151-02551
Type SOC25SO9CC11



Connector Clips feature various attachment point configurations to accommodate the many connectors on the market. They are first mated with a connector on a wire harness or cable assembly, then secured to a surface using the integrated mount. With so many configurations available, attachment surfaces can be a hole, edge, stud or even another harness assembly.

Length (imperial)	1.96 "
Length (metric)	50.0 mm
Width (imperial)	0.427 "
Width (metric)	10.85 mm

RoHS ✓

Material	Polyacetal (POM)
Operating Temperature	-40°F to +194°F (-40°C to +90°C)
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	5000
Carton Qty.	5000
Customs Number	3926909988