

TECHNICAL DATA SHEET

Part No. 151-02552
Article No. 151-02552
Type LOC10-14FTOVAL



The Locking Clamp is ideal for fastening wire and cable bundles to panels. Its uniquely engineered fir tree holds tightly in pre-stamped hole sizes from 9x12 mm to 9x14 mm. The locking clamp mechanism dynamically fits various bundle sizes, while an integrated cable tie saddle allows installers to add additional cable runs. The clamp is manufactured of an impact-modified Polyamide 6.6 material for increased flexibility, heat resistance and UV stabilization to deliver years of dependable performance. It is easy to install and operate with a single hand and does not require tools, saving time and labor costs.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	1000
Carton Qty.	1000
Customs Number	3926909988

Depth (imperial)	0.47 "
Depth (metric)	12.0 mm
Height (imperial)	1.71 "
Height (metric)	43.5 mm
Max. Bundle Diameter (imperial)	0.55 "
Max. Bundle Diameter (metric)	14.0 mm
Min. Bundle Diameter (imperial)	0.39 "
Min. Bundle Diameter (metric)	10.0 mm
Mounting Hole Diameter (imperial)	0.24 x 0.48 ", 0.26 x 0.49 ", 0.26 x 0.51 ", 0.28 x 0.47 "
Mounting Hole Diameter (metric)	6.2 x 12.2 mm, 6.5 x 12.5 mm, 6.5 x 13.0 mm, 7.0 x 12.0 mm
Panel Thickness (imperial)	0.02 - 0.27 "
Panel Thickness (metric)	0.6 - 6.75 mm
Width (imperial)	0.47 "
Width (metric)	12.0 mm

