

TECHNICAL DATA SHEET

Part No. 151-02567
Article No. 151-02567
Type MCAFLM30-1



Aluminum frame mounts can be used with 20, 30 or 40 mm square frames from the major aluminum frame manufacturers. As there is no need to screw them in place, these mounts offer maximum ease of use and fast installation. The mounts contain metal particles for detection in processing plants where the potential for contamination is undesirable.

Material	Polyamide 6.6, metal detectable (PA66MD)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Blue (BU)
Pkg. Qty.	100
Carton Qty.	5000
Customs Number	3926909988

Height (imperial)	0.68 "
Height (metric)	17.2 mm
Length (imperial)	1.02 "
Length (metric)	26.0 mm
Panel Thickness (imperial)	0.10 - 0.12 "
Panel Thickness (metric)	2.5 - 3.0 mm
Width (imperial)	0.71 "
Width (metric)	18 mm
Width 2 (imperial)	0.24 "
Width 2 (metric)	6 mm

