

TECHNICAL DATA SHEET

Part No. 151-02569
Article No. 151-02569
Type MSC901



HellermannTyton's Metal Edge Clip provides an excellent alternative to managing wire and PV cables where plastic fasteners are not the preferred method. Designed for effortless insertion, the Metal Edge Clip has a high extraction force that tolerates extreme environments and provides assurance that the cables are secure on a panel. The Metal Edge Clip is simple to install and can easily be removed with a flathead screwdriver.

Material	Stainless Steel (SS304)
Operating Temperature	-112°F to +1000°F (-80°C to +538°C)
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Metal (ML)
Pkg. Qty.	100
Carton Qty.	5000
Customs Number	7326908695

Length (imperial)	0.73 "
Length (metric)	18.44 mm
Max. Cable Diameter (imperial)	0.291 "
Max. Cable Diameter (metric)	7.39 mm
Min. Cable Diameter (imperial)	0.161 "
Min. Cable Diameter (metric)	4.1 mm
Panel Thickness (imperial)	0.03 - 0.05 "
Panel Thickness (metric)	0.76 - 1.24 mm
Width (imperial)	0.460 "
Width (metric)	11.57 mm

