

TECHNICAL DATA SHEET

Part No. 151-02587
Article No. 151-02587
Type 120MINICHNLFT6.5



HellermannTyton Mini Channels provide protection and configurable routing in a cost-effective solution. The variety of sizes and configurations enables engineers and installers to create optimum routing scenarios. Mini channels replace engineered channels that are costly to design and develop.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	856
Carton Qty.	856
Customs Number	3926909988

Fixation Method	Fir tree for round holes
Length (imperial)	3.01 "
Length (metric)	76.53 mm
Mounting Hole Diameter (imperial)	0.24 - 0.28 "
Mounting Hole Diameter (metric)	6.1 - 7.0 mm
Panel Thickness (imperial)	0.02 - 0.17 "
Panel Thickness (metric)	0.5 - 4.25 mm
Width (imperial)	0.765 "
Width (metric)	19.44 mm

