

TECHNICAL DATA SHEET

Part No. 151-02741
Article No. 151-02741
Type SOC18OS-21FT6.5



Tape clips are designed to provide simple and easy methods of securing cable bundles, hoses, or pipes.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature, 500h	+329°F (+165°C)
Operating Temperature, 1000h	+320°F (+160°C)
Operating Temperature, 5000h	+257°F (+125°C)
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	2000
Carton Qty.	2000
Customs Number	3926909988

Height (imperial)	0.976 "
Height (metric)	24.8 mm
Length (imperial)	1.57 "
Length (metric)	40.0 mm
Mounting Hole Diameter (imperial)	0.24 - 0.28 "
Mounting Hole Diameter (metric)	6.1 - 7.0 mm
Offset Length (imperial)	0.708 "
Offset Length (metric)	18.0 mm
Tape Bar Length (metric)	40.0 mm
Width (imperial)	1.03 "
Width (metric)	26.2 mm

RoHS 