

# TECHNICAL DATA SHEET

**Part No.** 151-02896  
**Article No.** 151-02896  
**Type** CC11B



Connector Clips feature various attachment point configurations to accommodate the many connectors on the market. They are first mated with a connector on a wire harness or cable assembly, then secured to a surface using the integrated mount. With so many configurations available, attachment surfaces can be a hole, edge, stud or even another harness assembly.

<b>Material</b>	Polyphenylene Sulfide (PPS)
<b>Operating Temperature</b>	-40°F to +302°F (-40°C to +150°C)
<b>UV Resistant</b>	No
<b>Use Conditions</b>	For Indoor and Outdoor Use
<b>Color</b>	Silver (SR)
<b>Pkg. Qty.</b>	5000
<b>Carton Qty.</b>	5000
<b>Customs Number</b>	3926909988

<b>Fixation Method</b>	Fir Tree for oval holes
<b>Length (imperial)</b>	1.18 "
<b>Length (metric)</b>	30.0 mm
<b>Mounting Hole Diameter (imperial)</b>	0.35 x 0.67 "
<b>Mounting Hole Diameter (metric)</b>	9.0 x 17.0 mm
<b>Panel Thickness (imperial)</b>	0.02 - 0.23 "
<b>Panel Thickness (metric)</b>	0.6 - 6.0 mm
<b>Width (imperial)</b>	0.72 "
<b>Width (metric)</b>	18.20 mm

