

TECHNICAL DATA SHEET

Part No. 151-02977
Article No. 151-02977
Type FMB4APT-A



HellermannTyton FlexTack Adhesive Cable Tie Mounts deliver excellent mounting performance on flat, curved and moderately angled surfaces. Use in combination with 18- through 50-pound cable ties to provide stability when securing bundles. The adhesive on this mount is approved for use on low- to medium-energy surfaces in automotive applications, such as clear-coats and plastics; railway, aerospace and heavy equipment; and where drilling a hole is not possible or desirable. The 4-way saddle allows cable ties to be inserted parallel or perpendicular to the wire bundles.

Material	Polyamide 6.6 heat stabilized (PA66HS)
Adhesive	Acrylate with base of acrylic foam
Operating Temperature	-40°F to +194°F (-40°C to +90°C)
Flammability	UL 94 V-2 (excluding adhesive)
Halogen Free	Yes
Use Conditions	For Indoor Use Only
Color	White (WH)
Pkg. Qty.	100
Carton Qty.	5000
Customs Number	3926909988

Fixation Method	Adhesive
For Cable Tie Series	T18 - T50
Height (imperial)	0.25 "
Height (metric)	6.3 mm
Length (imperial)	1.1 "
Length (metric)	28.0 mm
Max. Static Load (imperial)	1.1 lbf-ft
Maximum Static Load (N)	1.49 N
Width (imperial)	1.1 "
Width (metric)	28.0 mm

