

TECHNICAL DATA SHEET


Part No. 151-03101
Article No. 151-03101
Type LPM25



Low-profile mounts secure bundles close to mounting surfaces, making them ideal for applications where bundle mounting space is limited. These are secured to the mounting surface with a 0.25" mechanical fastener and feature a counter bore for easy access with a socket. The mount accommodates cable ties up to 0.5" in width. Low fire hazard material is designed specifically for rail applications.

Material	Polyamide 6.6/6, V0 (PA666V0)
Operating Temperature	-40°F to +248°F (-40°C to +120°C)
Flammability	UL 94 V-0
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	500
Carton Qty.	500
Customs Number	3926909988

Fixation Method	Screw Mounting and Rivet
For Cable Tie Series	T50 - T250
Height (imperial)	0.66 "
Height (metric)	16.7 mm
Length (imperial)	1.8 "
Length (metric)	45.1 mm
Mounting Screw Type	1/4" (M6) Screw
Width (imperial)	0.98 "
Width (metric)	24.9 mm



ASTM

NFPA 130