

TECHNICAL DATA SHEET

Part No. 151-03102
Article No. 151-03102
Type CTM4



Designed specifically for holding heavier cable bundles these mounting bases can be used in many industries from agriculture to truck manufacture. They offer a very secure fixing and can be used with a wide variety of heavy duty cable ties up to 8.3 mm width.

Material	Polyamide 6.6/6, V0 (PA666V0)
Operating Temperature	-40°F to +248°F (-40°C to +120°C)
Flammability	UL 94 V-0
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	100
Carton Qty.	5000
Customs Number	3926909988

Fixation Method	Screw Mount
For Cable Tie Series	T18 - T120
Height (imperial)	0.37 "
Height (metric)	9.4 mm
Length (imperial)	0.86 "
Length (metric)	21.8 mm
Max. Cable Tie Width (imperial)	0.31 "
Max. Cable Tie Width (metric)	7.8 mm
Mounting Hole Diameter (imperial)	0.25 "
Mounting Hole Diameter (metric)	6.4 mm
Mounting Screw Type	1/4" (M6) Screw
Width (imperial)	0.62 "
Width (metric)	15.8 mm

HF ✓

LFH ✓

RoHS ✓

ASTM

NFPA 130