

TECHNICAL DATA SHEET

Part No. 151-03404
Article No. 151-03404
Type EC14



HellermannTyton's edge clips are designed specifically to route bundles by securing them to the edge of a plastic or metal sheet without the need for a mounting hole. These edge clips are molded to a tape bar, which can be secured to cables with cable ties or tape. The clip is easy to secure, and the extraction force is high due to the integrated metal clamp that holds the edge clip in place.

Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 HB
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	500
Carton Qty.	8000
Customs Number	3926909988

Fixation Method	Edge Clip
Height (imperial)	0.49 "
Height (metric)	12.4 mm
Length (imperial)	1.6 "
Length (metric)	40.0 mm
Panel Thickness (imperial)	0.04 - 0.12 "
Panel Thickness (metric)	1.0 - 3.0 mm
Tape Bar Length (metric)	40.0 mm
Width (imperial)	0.39 "
Width (metric)	10.0 mm

