

TECHNICAL DATA SHEET

Part No. 151-03473
Article No. 151-03473
Type BC56FT6.5



HellermannTyton's bundling clips allow a harness to be routed around a corner and attached to the panel at this location.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	2500
Carton Qty.	2500 box
Customs Number	3926909988

Fixation Method	Fir tree for round holes
Height (imperial)	0.77 "
Height (metric)	19.7 mm
Length (imperial)	2.20 "
Length (metric)	56.0 mm
Mounting Hole Diameter (imperial)	0.24 - 0.28 "
Mounting Hole Diameter (metric)	6.1 - 7.0 mm
Panel Thickness (imperial)	0.02 - 0.23 "
Panel Thickness (metric)	0.6 - 6.0 mm
Tape Bar Length (imperial)	2.20 "
Tape Bar Length (metric)	56.0 mm
Width (imperial)	0.31 "
Width (metric)	8.0 mm

HF ✓

RoHS ✓