

Technical data sheet

Article number:**151-03512****CC7FT8LG**

Material	Polyamide 4.6 (PA46)
Colour	Black (BK)
CE Certification	No
Fixation Method	Fir Tree
Flammability	UL 94 HB
for Hole Ø (FH)	7.6 - 8.4 mm
Height (H)	20.7 mm
Length (L)	24.2 mm
Operating Temperature	-40 °C to +130 °C
Package Content	3000 pcs.
Package Content packed in	carton
Panel Thickness	0.60 - 6.0 mm
Panel Thickness max.	6.0 mm
Panel Thickness min.	0.60 mm
ROHS compliant	Yes
Width (W)	7.45 mm

