

# TECHNICAL DATA SHEET

**Part No.** 151-03642  
**Article No.** 151-03642  
**Type** MAGC10S



Magnetic clips are designed to route bundles by securing to steel surfaces without the need for a mounting hole. Simply attach the wire bundle by pushing it into the clip and position it onto the beam, metal joist, ceiling channel, conveyor frame, or other steel surface. The clips are simple to secure and can attach to surfaces contaminated with oil or debris. Ultra-strong neodymium magnets are ideal as a permanent mount or for temporary applications. Reuse and reposition them for ultimate flexibility without needing to replace or repurchase parts.

<b>Material</b>	Neodymium alloy 35M (NDFEB35M), Polyacetal (POM), Steel (ST)
<b>Operating Temperature</b>	-40°F to +176°F (-40°C to +80°C)
<b>Halogen Free</b>	Yes
<b>Plenum Rating</b>	AH-2
<b>UV Resistant</b>	No
<b>Use Conditions</b>	For Indoor Use Only
<b>Color</b>	White (WH)
<b>Pkg. Qty.</b>	100
<b>Carton Qty.</b>	1200 Pieces
<b>Customs Number</b>	8505110070

<b>Depth (imperial)</b>	0.15 "
<b>Depth (metric)</b>	3.9 mm
<b>Diameter (imperial)</b>	0.75 "
<b>Diameter (metric)</b>	19.0 mm
<b>Height (imperial)</b>	0.73 "
<b>Height (metric)</b>	18.5 mm
<b>Length (imperial)</b>	0.62 "
<b>Length (metric)</b>	15.8 mm
<b>Magnetic pull strength (lb/ft)</b>	10 lbf-ft
<b>Magnetic pull strength (N)</b>	44 N
<b>Nominal Bundle Diameter (imperial)</b>	0.5 "
<b>Nominal Bundle Diameter (metric)</b>	12.7 mm
<b>Rotation (°)</b>	360 °

