

TECHNICAL DATA SHEET

Part No. 151-03647
Article No. 151-03647
Type MAGCLMP15L



Magnetic clamps route bundles by securing to steel surfaces without the need for a mounting hole. Simply enclose the wire bundle in the clamp, close the locking clip, and position it onto the beam, metal joist, ceiling channel, conveyor frame, or other steel surface. Magnetic clamps are simple to secure and can attach to surfaces contaminated with oil or debris. Ultra-strong neodymium magnets are ideal as a permanent mount or for temporary applications. Reuse and reposition them for ultimate flexibility without needing to replace or repurchase parts.

Material	Neodymium alloy 45M (NDFEB45M), Polyacetal (POM), Steel (ST)
Operating Temperature	-40°F to +176°F (-40°C to +80°C)
Halogen Free	Yes
Plenum Rating	AH-2
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Black (BK)

Pkg. Qty.	10
Carton Qty.	500 Pieces
Customs Number	8505110070

Diameter (imperial)	0.91 "
Diameter (metric)	23.2 mm
Height (imperial)	0.85 "
Height (metric)	21.5 mm
Magnetic pull strength (lb/ft)	15 lbf-ft
Magnetic pull strength (N)	66 N
Nominal Bundle Diameter (imperial)	0.50 "
Nominal Bundle Diameter (metric)	12.7 mm
Rotation (°)	360 °

