

# TECHNICAL DATA SHEET

**Part No.** 151-03655  
**Article No.** 151-03655  
**Type** MAGJH90TXS



Magnetic J-hooks route cables by securing to steel surfaces without the need for a mounting hole. Simply hang cables within the J-hook and position the magnet onto the beam, metal joist, ceiling channel, conveyor frame, or other steel surface. Magnetic J-hooks are ideal for supporting communication and data cables. The mounts are simple to secure and can attach to surfaces contaminated with oil or debris. Ultra-strong neodymium magnets are ideal as a permanent mount or for temporary applications. Reuse and reposition them for ultimate flexibility without needing to replace or repurchase parts.

<b>Diameter (metric)</b>	40.0 mm
<b>Height (imperial)</b>	4.95 "
<b>Height (metric)</b>	125.8 mm
<b>Magnetic pull strength (lb/ft)</b>	90 lbf-ft
<b>Magnetic pull strength (N)</b>	400 N
<b>Nominal Bundle Diameter (imperial)</b>	0.56 "
<b>Nominal Bundle Diameter (metric)</b>	14.2 mm
<b>Rotation (°)</b>	360 °

<b>Material</b>	Neodymium alloy 45M (NDFEB45M), Steel (ST)
<b>Operating Temperature</b>	-40°F to +176°F (-40°C to +80°C)
<b>Halogen Free</b>	Yes
<b>Plenum Rating</b>	AH-2
<b>UV Resistant</b>	No
<b>Use Conditions</b>	For Indoor Use Only
<b>Color</b>	Metal (ML)

<b>Pkg. Qty.</b>	10
<b>Carton Qty.</b>	100 Pieces
<b>Customs Number</b>	8505110070

HF ✓

RoHS ✓