

TECHNICAL DATA SHEET

Part No. 151-03790
Article No. 151-03790
Type HDC19x2



This clamp system can protect HV cable wires in double cable routing applications and is secured using hardware. Clamp halves are sold individually; order two of these parts for every one clamp desired.

Material	Polyamide 6.6 glass fiber reinforced (PA66GF15), Thermoplastic Elastomer (TPE)
Operating Temperature	-40°F to +257°F (-40°C to +125°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Black (BK)
Pkg. Qty.	400
Carton Qty.	400 Pieces
Customs Number	3926909988

Height (imperial)	1.42 "
Height (metric)	36.0 mm
Length (imperial)	3.24 "
Length (metric)	82.3 mm
Length 2 (imperial)	1.73 "
Length 2 (metric)	44.0 mm
Max. Bundle Diameter (imperial)	0.77 "
Max. Bundle Diameter (metric)	19.5 mm
Max. Bundle Diameter First Hole (imperial)	0.77 "
Max. Bundle Diameter First Hole (metric)	19.5 mm
Max. Bundle Diameter Second Hole (imperial)	0.77 "
Max. Bundle Diameter Second Hole (metric)	19.5 mm
Mounting Hole Centers (imperial)	1.73 "
Mounting Hole Centers (metric)	44.0 mm
Mounting Hole Diameter (imperial)	0.31 x 0.05 "
Mounting Hole Diameter (metric)	M8
Width (imperial)	1.02 "
Width (metric)	26.0 mm

