

TECHNICAL DATA SHEET

Part No. 151-03823
Article No. 151-03823
Type MOC19FT6.5



The MOC with Round Fir Tree features HellermannTyton's unique retention clip with an integrated fir tree to fit securely in a 6.5 (+/-0.4) mm hole. The mount delivers a low insertion force while exhibiting high extraction resistance for a secure mounting point against a panel.

| | |
|------------------------------|--|
| Material | Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV) |
| Operating Temperature | -40°F to +221°F (-40°C to +105°C) |
| Flammability | UL 94 HB |
| Halogen Free | Yes |
| UV Resistant | Yes |
| Use Conditions | For Indoor and Outdoor Use |
| Color | Black (BK) |
| Pkg. Qty. | 100 |
| Carton Qty. | 3000 |
| Customs Number | 3926909988 |

| | |
|--|-----------------------------------|
| Depth (imperial) | 0.47 " |
| Depth (metric) | 12.0 mm |
| Height (imperial) | 1.91 " |
| Height (metric) | 48.5 mm |
| Max. Bundle Diameter (imperial) | 0.86 " |
| Max. Bundle Diameter (metric) | 21.8 mm |
| Min. Bundle Diameter (imperial) | 0.67 " |
| Min. Bundle Diameter (metric) | 17.0 mm |
| Mounting Hole Diameter (imperial) | 0.24 - 0.27 ", 0.25 " (HEXAGONAL) |
| Mounting Hole Diameter (metric) | 6.1 - 6.9 mm, 6.35 mm (hexagonal) |
| Panel Thickness (imperial) | 0.02 - 0.22 " |
| Panel Thickness (metric) | 0.6 - 5.5 mm |

