

TECHNICAL DATA SHEET

Part No. 151-03828
Article No. 151-03828
Type SLRCN12SM38



This solar cable management device is designed specifically for GameChange Solar trackers. Once mounted, cables or tubes can be simply pushed in past the flexible retainer to nest, fully enclosed, within the 1.5 inch opening.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature, 500h	+329°F (+165°C)
Operating Temperature, 1000h	+320°F (+160°C)
Operating Temperature, 5000h	+257°F (+125°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	200
Carton Qty.	200
Customs Number	3926909988

Fixation Method	Screw Mount
Height (imperial)	2.83 "
Height (metric)	72.0 mm
Length (imperial)	2.44 "
Length (metric)	62.0 mm
Max. Bundle Diameter (imperial)	1.5 "
Max. Bundle Diameter (metric)	38.1 mm
Mounting Hole Diameter (metric)	M10 Threaded
Width (imperial)	1.89 "
Width (metric)	48.1 mm

