

TECHNICAL DATA SHEET

Part No. 151-03865
Article No. 151-03865
Type LOC10-14XECMOCF90



The Solar Locking Clamp with Edge Clip combines two of our most successful products into one – the Edge Clip and the Solar Locking Clamp – to provide a universal design that can fit on a wide variety of edges without the use of a cable tie. Fabricated specifically for solar applications, the Solar Locking Clamp can attach to a wide variety of solar panel and racking edge sizes. The locking clamp mechanism dynamically fits various bundle sizes. The clamp is manufactured of an impact-modified Polyamide 6.6 material for increased flexibility, heat resistance and UV stabilization to deliver years of dependable performance. It is easy to install and operate with a single hand and does not require tools, saving time and labor costs.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV), Polyamide 6.6, high impact modified, heat and UV-stabilized, proprietary blend (PA66HIRHSUVR5)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	1000
Carton Qty.	1000 Pieces
Customs Number	3926909988

Depth (imperial)	0.55 "
Depth (metric)	14.0 mm
Height (imperial)	2.25 "
Height (metric)	57.23 mm
Length (imperial)	1.19 "
Length (metric)	28.43 mm
Max. Bundle Diameter (imperial)	0.55 "
Max. Bundle Diameter (metric)	14.0 mm
Min. Bundle Diameter (imperial)	0.39 "
Min. Bundle Diameter (metric)	10.0 mm
Panel Thickness (imperial)	0.03 - 0.11 "
Panel Thickness (metric)	1.0 - 3.0 mm
Width (imperial)	0.47 "
Width (metric)	12.0 mm

