

TECHNICAL DATA SHEET

Part No. 151-03905
Article No. 151-03905
Type DHVC24M6



These clamps separate multiple bundles and secure them to any surface with a 6 mm stud or bolt. The one-piece hinged design snaps together to keep bundles such as tubing or battery cables separated. The robust design and durable materials also make it ideal for heavy duty applications.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	250
Carton Qty.	250 Pieces
Customs Number	3926909988

Height (imperial)	1.26 "
Height (metric)	32.0 mm
Length (imperial)	3.96 "
Length (metric)	100.5 mm
Max. Bundle Diameter (imperial)	0.94 "
Max. Bundle Diameter (metric)	24.0 mm
Max. Bundle Diameter First Hole (imperial)	0.94 "
Max. Bundle Diameter First Hole (metric)	24.0 mm
Max. Bundle Diameter Second Hole (imperial)	0.94 "
Max. Bundle Diameter Second Hole (metric)	24.0 mm
Mounting Hole Diameter (imperial)	0.24 "
Mounting Hole Diameter (metric)	M6
Width (imperial)	1.20 "
Width (metric)	30.5 mm

RoHS