

TECHNICAL DATA SHEET

Part No. 151-03907
Article No. 151-03907
Type MSC2



HellermannTyton's Heavy Duty Metal Edge Clip provides an excellent alternative to managing up to 2 wire and PV cables where plastic fasteners are not the preferred method. Designed for effortless insertion, the Heavy Duty Edge Clip has a high extraction force that tolerates extreme environments and provides assurance that the cables are secure on a panel. This Metal Edge Clip is simple to install and can easily be removed with a flathead screwdriver.

Material	Stainless Steel (SS304)
Operating Temperature	-112°F to +1000°F (-80°C to +538°C)
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Metal (ML)
Pkg. Qty.	100
Carton Qty.	5000 Pieces
Customs Number	7326908695

Length (imperial)	0.95 "
Length (metric)	24.1 mm
Max. Cable Diameter (imperial)	0.30 "
Max. Cable Diameter (metric)	7.6 mm
Min. Cable Diameter (imperial)	0.20 "
Min. Cable Diameter (metric)	5.0 mm
Panel Thickness (imperial)	0.04 - 0.12 "
Panel Thickness (metric)	1.0 - 3.0 mm
Width (imperial)	0.50 "
Width (metric)	13.0 mm

