

TECHNICAL DATA SHEET

Part No. 151-04007
Article No. 151-04007
Type CMRCCLM6



The Bolt Mount Ratchet Clamp offers versatility when managing conduit, wires, cables and hoses. It is specially designed for locations with space constraints or where offset mounting options are not ideal. Available with a compression limiter for crush resistance in high-torque applications, or in all-plastic for low- to medium-torque applications. The robust design and durable materials make it ideal for heavy duty applications, both indoors and out. The adjustable clamp can be closed by hand to the desired diameter. The release feature allows easy and nondestructive removal or addition of cables simply by inserting a flat-head screwdriver. In this way, the clamp can be reused without removing it from the mounting surface.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature, 500h	+329°F (+165°C)
Operating Temperature, 1000h	+320°F (+160°C)
Operating Temperature, 5000h	+257°F (+125°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	25
Carton Qty.	150 Pieces
Customs Number	3926909988

Fixation Method	Screw Mount
Length (imperial)	4.93 "
Length (metric)	125.22 mm
Max. Bundle Diameter (imperial)	1.42 "
Max. Bundle Diameter (metric)	36.1 mm
Min. Bundle Diameter (imperial)	0.76 "
Min. Bundle Diameter (metric)	19.3 mm
Min. Tensile Strength (imperial)	250 lbs
Mounting Hole Diameter (imperial)	0.248 "
Mounting Hole Diameter (metric)	6.3 mm
Width (imperial)	1.38 "
Width (metric)	35.1 mm

