

TECHNICAL DATA SHEET

Part No. 151-04030
Article No. 151-04030
Type MAGC10M



Magnetic clips are designed to route bundles by securing to steel surfaces without the need for a mounting hole. Simply attach the wire bundle by pushing it into the clip and position it onto the beam, metal joist, ceiling channel, conveyor frame, or other steel surface. The clips are simple to secure and can attach to surfaces contaminated with oil or debris. Ultra-strong neodymium magnets are ideal as a permanent mount or for temporary applications. Reuse and reposition them for ultimate flexibility without needing to replace or repurchase parts.

Material	Neodymium alloy 35M (NDFEB35M), Polyacetal (POM), Steel (ST)
Operating Temperature	-40°F to +176°F (-40°C to +80°C)
Halogen Free	Yes
Plenum Rating	AH-2
Use Conditions	For Indoor Use Only
Color	Black (BK)
Pkg. Qty.	100
Carton Qty.	1000 Pieces
Customs Number	8505110070

Depth (imperial)	0.23 "
Depth (metric)	5.7 mm
Diameter (imperial)	0.75 "
Diameter (metric)	19 mm
Height (imperial)	0.97 "
Height (metric)	24.7 mm
Length (imperial)	1.03 "
Length (metric)	26.2 mm
Magnetic pull strength (lb/ft)	10 lbf-ft
Magnetic pull strength (N)	44 N
Nominal Bundle Diameter (imperial)	0.75
Nominal Bundle Diameter (metric)	19.05 mm
Rotation (°)	360 °

