

TECHNICAL DATA SHEET

Part No. 151-04041
Article No. 151-04041
Type MAGJH90TL



Magnetic J-hooks route cables by securing to steel surfaces without the need for a mounting hole. Simply hang cables within the J-hook and position the magnet onto the beam, metal joist, ceiling channel, conveyor frame, or other steel surface. Magnetic J-hooks are ideal for supporting communication and data cables. The mounts are simple to secure and can attach to surfaces contaminated with oil or debris. Ultra-strong neodymium magnets are ideal as a permanent mount or for temporary applications. Reuse and reposition them for ultimate flexibility without needing to replace or repurchase parts.

Material	Neodymium alloy 45M (NDFEB45M), Steel (ST)
Operating Temperature	-40°F to +176°F (-40°C to +80°C)
Halogen Free	Yes
Plenum Rating	AH-2
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Zinc-plated Metal (BV)
Pkg. Qty.	10
Carton Qty.	100 Pieces
Customs Number	8505110070

Height (imperial)	4.82 "
Height (metric)	122.34 mm
Magnetic pull strength (lb/ft)	90 lbf-ft
Magnetic pull strength (N)	400 N
Nominal Bundle Diameter (imperial)	2
Nominal Bundle Diameter (metric)	50.8 mm
Rotation (°)	360 °

