

TECHNICAL DATA SHEET

Part No. 151-04074
Article No. 151-04074
Type SGROC15.5-20CLIP17



The Ratchet O-Clamp is designed for tight spaces, maintaining a low-profile, adjustable grip around a routing while providing a robust mounting solution. Designed for fluid routing and high-voltage cable management, this clamp includes a TPE liner to protect the routing and keep it in position. HellermannTyton's connector clips provide a single method to mount connectors to various surfaces in a variety of applications. Clips can be paired with brackets for custom routing needs.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV), Thermoplastic Elastomer (TPE)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)

Pkg. Qty.	1000
Carton Qty.	1000 Pieces
Customs Number	3926909988

Connection Type	USCAR17
Fixation Method	Connector Clip
Length (imperial)	2.29 "
Length (metric)	58.1 mm
Max. Bundle Diameter (imperial)	0.79 "
Max. Bundle Diameter (metric)	20.0 mm
Min. Bundle Diameter (imperial)	0.61 "
Min. Bundle Diameter (metric)	15.5 mm
Min. Tensile Strength (imperial)	100 lbs
Min. Tensile Strength (metric)	445 N
Width (imperial)	0.81 "
Width (metric)	20.5 mm

